

KT88 National Gold Tube

KT88 National Gold Tube

Voltages applied to the tube: Filament Voltage 6.3V

Plate Voltage 250V Screen Grid Voltage 250V Control Grid Voltage -15V

Limits: Max. Noise Level 800µVrms

Max. Microphonics 4.0 mVrms

A tube with a noise level greater than 800 µVrms would be rejected.

Microphonics are measured while the tube is being tapped. A tube with a microphonics measurement of 4.0 mVrms or less is accepted, while a tube with a measurement greater than 4.0 mVrms is rejected.

Output Current Scales For Matching

No.		No.	
1.	86.0 mA - 89.0 mA	6.	101.1 mA - 104.0 mA
2.	89.1 mA - 92.0 mA	7.	104.1 mA - 107.0 mA
3.	92.1 mA - 95.0 mA	8.	107.1 mA - 110.0 mA
4.	95.1 mA - 98.0 mA	9.	110.1 mA - 113.0 mA
5.	98.1 mA - 101.0 mA		10. 113.1 mA - 116.0 mA